

TG ELECTRONICS

Disposal tower
EMS-CLEAN



Disposal tower EMS-CLEAN

DESCRIPTION

The innovative disposal tower allows an easy, ergonomic and clean emptying process of cassette toilets. The use of stainless steel combined with a small footprint provide a modern and attractive design. Over and above that, the robust construction and the use of high quality components lead to a long product life, less service expenditure and very good weather resistance.

OPERATION

After inserting a coin or paying by NFC-card the available usage time is displayed. By opening the disposal flap, the countdown of the available time is activated and the cleaning process is started: During this time, the continuous flush is activated so that the cassette toilet can be emptied clean and simple.

Afterwards, the cassette toilet can be flushed with water by positioning the spout under the faucet and by pressing the flat foot switch near the ground. After finishing the disposal process the flap can be closed to reduce odors.





Figure:
Disposal flap in open and closed state

FEATURES


- Innovative drain construction with integrated flush
- Extra fauced with ergonomic foot switch activation
- Robust and weather resistant stainless steel housing
- Intuitive operation
- Encapsulated electronics
- Info display for remaining time and parameters
- Electronic coin selector 0,10 EUR to 2,- EUR and tokens
- Dimensions (HxWxD): 1300 x 260 x 275 mm

OPTIONS

- Terminal for cashless payments without PIN entry
 - Acceptance of NFC bank cards & smartphones
 - SIM card and antenna for wireless data transmission
 - Remote display of sales data
- Contactless payment by Beckmann RFID card
- LED illumination for night operation
- Winter kit with pipe heating
- Flush control for external bottom valve







Tlf: 91795392
 Blåbærdalen 30 6518 Kr.sund N.
 e-mail: post@tgelectronics.no
www.tgelectronics.no



EMS-CLEAN

Operating procedure






Tlf: 91795392


Vidhaugen 114 7550 Hommelvik

e-mail: post@tgelectronics.no

EMS-CLEAN EL-TILKOBLING



Strøm tilførsel ems-clean
1 fase 230V 16A, kurs med
jordfeilbryter



VIKTIG:

Husk å ha strømkabelen så lang, at man kan ha servicemuligheter på utstyret inne i ems-clean.

Ved service/testing henger man opp ISO-boksen slik, så får man grei tilgang til de andre komponentene.



Tlf: 91795392

Vidhaugen 114 7550 Hommelvik

e-mail: post@tgelectronics.no

EMS-CLEAN VANN-AVLØP TILKOBLING



Vann og avløps tilkobling. Antall vanntilkoblinger varierer etter hvor mange funksjoner-spylings muligheter dere velger.



Man må vurdere sammen med VVS rørlegger om dere lokalt skal ha montert vannlås. Ems-clean har ikke vannlås i seg.

Dette gjelder også tømmerist og tømmeventil.

Husk vannlåsen må monteres frostsikkert, og helst være mulighet for service.



VANNLÅS FOR EMS-CLEAN




Fig. 5-3 Foundation disposal tower

